# Specification Sheet

Part Number: PBM10M4



Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel.

The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.

Push-Button Cable Tie Mount, 0.25" Hole Dia, 0.12" Max Panel, 0.2" Max Tie Width, PA66, White, 1000/pkg

| | |
|---|---|
| Article Number | 151-00231 |
| Type | PBM |
| Color | White (WH) |
| Quantity Per | pack |
| Product Description | HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas. |
| Short Description | Push-Button Cable Tie Mount, 0.25" Hole Dia, 0.12" Max Panel, 0.2" Max Tie Width, PA66, White, 1000/pkg |
| Global Part Name | PBM-PA66-WH |

Downloaded from Arrow.com.

| | |
|---|---|
| Length L (Metric) | 10.7 |
| Fixation Method | Push Mount |
| Width W (Imperial) | 0.26 |
| Width W (Metric) | 6.6 |
| Cable Ties | T18 - T50 |
| Height H (Imperial) | .40 |
| Height H (Metric) | 10.20 |
| Cable Tie Width Max (Imperial) | 0.2 |
| Cable Tie Width Max (Metric) | 5.0 |
| Panel Thickness Min (Imperial) | 0.118 |
| Panel Thickness Max (Imperial) | 0.12 |
| Panel Thickness Min (Metric) | 3.0 |
| Panel Thickness Max (Metric) | 3.0 |
| Mounting Hole Diameter D (Imperial) | 0.25 - 0.26 " |
| Mounting Hole Diameter D (Metric) | 6.25 - 6.55 mm |
| Mounting Hole Diameter D Min (Imperial) | 0.25 |

Downloaded from Arrow.com.

| | |
|---|---|
| Mounting Hole Diameter D Max (Imperial) | 0.26 |
| Mounting Hole Diameter D Max (Metric) | 6.55 |
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL 94 V-2 |
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor Use Only |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | UL |
| UL Recognized (US) | Yes |
| UL Recognized (US and Canada) | Yes |
| Package Quantity (Imperial) | 1000 |
| Package Quantity (Metric) | 1000 |

Downloaded from Arrow.com.

| | |
|---|---|
| Customs Number | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.



Downloaded from Arrow.com.