



Part Number : [1300580057](#)

Product Description : RJ-Lnxx RJ45 Female to RJ45 Female Adaptor

Series Number : 130058

Status : Active

Product Category : Circular Industrial Connectors

Engineering Part Number : RJBG16821




Documents and Resources

Drawings

[1300580057_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130058
Description	RJ-Lnxx RJ45 Female to RJ45 Female Adaptor
IP Rating	IP67
Product Name	RJ-Lnxx
Type	In-Line Interconnect
UPC	78678850240

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V DC

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	Delrin
Material - Contact	N/A
Material - Coupling Nut	Nylon
Material - Plating Mating	N/A
Net Weight	44.700/g
Orientation	Straight

Poles	N/A
Temperature Range - Operating	-20° to +80°C
Wire Size (AWG)	N/A

This document was generated on May 22, 2026