

Part Number : [1301490019](#)

Product Description : Safeway Flanged Receptacle with Locking Blade, 3 Pole/3 Wire, Non-NEMA, 15A/125V, 10A/250V

Series Number : 130149

Status : Active

Product Category : Wiring Devices

Engineering Part Number : 2507MB



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130149
Description	Safeway Flanged Receptacle with Locking Blade, 3 Pole/3 Wire, Non-NEMA,15A/125V, 10A/250V
IP Rating	N/A
NEMA Configuration	Non-NEMA Locking
Product Name	Safeway
Specialty	N/A
Type	Receptacle
UPC	78678870501

Electrical

Current - Maximum per Contact	10.0A, 15.0A
GFCI	No
Voltage - Maximum	125V / 250V

Physical

Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	3-pole/3-wire
Receptacle Type	Single

This document was generated on Dec 29, 2025