Part Number : 732511354
Product Description : SMA Jack, Straight, PCB Receptacle, Surface Mount, Nickel (Ni) Plated, Tape and Reel (400 Pieces), 50 Ohms
Series Number : 73251
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

732511354_sd.pdf

SD-73251-135-PKG-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-89675-346-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)4578-DC (25 June 2020)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73251
Description	SMA Jack, Straight, PCB Receptacle, Surface Mount, Nickel (Ni) Plated, Tape and Reel (400 Pieces), 50 Ohms
Application	RF
Product Name	SMA
Style	PCB
Type	Subminiature
UPC	887191482293

Electrical

Frequency	18 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.270/g
Orientation	Straight

Downloaded from Arrow.com.

Packaging Type	Embossed Tape on Reel
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount
PCB Thickness - Recommended	N/A
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.