

[+ PASSIVE COMPONENTS](#)

SURFACE MOUNT RESISTORS



✓ Active

↓ **3D PDF**

> [See All Documentation](#)

TE CONNECTIVITY (TE)

TLR 2512 2.0W R10 1% 75PPM 2K RL

[CGS](#) | [TLR](#)

[TLR3A20WR10FTDG](#)

TE Internal Number: 5-2176166-0

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Resistor Type **Current Sensing Resistor**

Number of Terminations **2**

Size Code **2512**

Packaging Method **Taped & Reeled**

Tolerance **1%**

> [See All Features](#)

North America ▼

Contact us to request pricing, availability and customization options.

REQUEST ADDITIONAL INFORMATION



GET SAMPLE



SAVE TO LIST ▼



CHECK FOR TOOLING



FIND SIMILAR PRODUCTS



DOCUMENTATION

FEATURES

PRODUCT COMPLIANCE

CAD Files

3D PDF

PDF

3D

[Customer View Model](#)

2D_DXF.ZIP

English

[Customer View Model](#)

3D_IGS.ZIP

English

[Customer View Model](#)

3D_STP.ZIP

English

Also in the Series | [TLR](#)



Surface Mount Resistors
(102)



Time Delay Relays (1)

Customers Also Bought

SURFACE MOUNT RESISTORS	SURFACE MOUNT RESISTORS	THROUGH-HOLE RESISTORS	SURFACE MOUNT RESISTORS
CPF 0603 1K21 0.1% 25PPM 1K RL CPF0603B1K21E1	CPF 0603 196K 0.1% 25PPM 1K RL CPF0603B196KE1	LR2 1% 430K LR2F430K	CPF 0603 205K 1% 50PPM 1K RL CPF0603F205KC1

About TE Connectivity	For Partners	Customer Support	CALL US	LIVE CHAT	United States
Our Company Events TE News Center Careers Investors Corporate Responsibility Terms and Conditions of Sale	Distributors Suppliers	Email or Call Us Find Authorized Distributors What's New on TE.com Product FAQs Share Feedback			Select Country & Language United States (EN) Germany (DE) China (中文) Japan (日本語) Afghanistan (EN) ▼ Find Your Country ▼