

## Technical data sheet

Article number:  
300-73160

TCN20-6.6/2.4



<b>Product Group</b>	Heat shrinkable tubing 3:1 - Self extinguishing
<b>Product Family</b>	TCN20 overexpanded
<b>Material</b>	Polyolefin, cross-linked (PO-X)
<b>Colour</b>	Black (BK)
<b>Dielectric Strength [Test method]</b>	20 kV/mm [IEC 243]
<b>Elongation at break (min.)</b>	400 %
<b>Elongation At Heat Aging</b>	350 %
<b>Flammability</b>	UL 224 VW-1
<b>Heat Aging Test</b>	168h/160°C
<b>Longitudinal Change After Shrinkage</b>	+/-5%
<b>Min. Shrink Temperature - °C</b>	+100 °C
<b>Minimum Tensile Strength At Heat Aging</b>	14 MPa
<b>Operating Temperature</b>	-55 °C to +125 °C
<b>Package Content</b>	300 m
<b>Package Content packed in</b>	reel
<b>Recov. Ø d max.</b>	2.4 mm
<b>Shrink Ratio</b>	3:1
<b>Specifications</b>	C22.2 no. 198.1-06, CSA -C22.1, DIN 75200 (09/1980), DIN EN 60068-1/03.95, IEC 60068-1/88 & 92, VW 80000/2009-10
<b>Supplied Ø D min.</b>	6.6 mm
<b>Tensile Strength</b>	14 MPa
<b>UL-File Number</b>	E143529
<b>Wall (WT)</b>	0.5 mm

RoHS

