




Connector Location A


Connector Location B



Loading-Plan



X
male



- Protection level: IP65/67
- Temperature range: -40°C ... +70°C

 All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by STOCHECIC Stocheci	Inspected by COSTEA Costea	Standardisation MUNTEANV Muntean	Date 2018-05-29	State Final Release	
Department HCS - RO		Title HARTING PushPull RJ45 Cable Assembly				Doc-Key / ECM-Nr. 100084477/UGD/008/D 500000135635	
HARTING Customised Solutions D-32339 Espelkamp		Type TB	Number 09473700XXX			Rev. D	Page 1/2

[illegible]