

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NUMBER*	WEIGHT lbs/100 pcs (g)/100 pcs	USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS
ABM100-AT	0.26 (119)	M, I, S



ADHESIVE BACKING: ACRYLIC BASED ADHESIVE PRESSURE SENSITIVE FOAM TAPE 0.04 (1.0) THICK WITH A PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.50 lbs (227g) MAX. WEIGHT ON A CLEAN DRY SMOOTH SURFACE.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND / OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



NOTES:
1. SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.
2. THE '-AT' SUFFIX REPRESENTS ACRYLIC ADHESIVE.
3. MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 180°F(82°C).
4. SUPPLIED IN STRIPS OF TWO.
5. HOLE FOR STANDARD S6 FLAT HEAD SCREW.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
08	2/16/23	BWG	MPH	JADE	A CORRECTED METRIC CONVERSION DIMENSION	128823/00
07	10/22/14	BWG	MPH	JADE	REMOVED RAISED PANDUIT MARK FROM PART, UPDATED NOTE 1 AND TITLE BORDER AND CREATED NEW CAD ID, WAS G00033BB_DC_ABM100AT_06	GB0033BB/07

TITLE

ABM100-AT - FOUR-WAY MOUNT

CUSTOMER DRAWING

ITEM REVISION NAME: 10B0150K/01

DATASET FILE NAME: 10B0150K_DC/01 GB0033BB r08

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]

.x ± 0.05 [1.3] .xxx ± 0.010 [0.25]

.xx ± 0.02 [.02] ANGLES ± 5 °

THIRD ANGLE PROJECTION

MATERIAL: NYLON 6/6

DRAWING NUMBER: GB0033BB

DRAWN BY	DATE	CHK	SCALE	SIZE
MJK	12/09/92		NONE	A

SHT 1 OF 1

Downloaded from Arrow.com.