

✔ Active

PRODUCT DRAWING
English

3D PDF

TE CONNECTIVITY (TE)

025 12POS CAP ASSY V TIN

> View All Products (396)

Always EU RoHS/ELV Compliant

Number of Positions **12**

Centerline (Pitch) **2.2 mm [.087 in]**

Sealable **No**

Mounting Orientation **Vertical/180°**

Number of Rows **2**

1473898-6

TE Internal Number: 1473898-6

TH/.025 Connector System

North America

Contact us to request pricing, availability and customization options.

REQUEST ADDITIONAL INFORMATION

CONTACT US

GET SAMPLE

Downloaded from Arrow.com.

ADD TO LIST

DOCUMENTATION

Product Drawings

0.64(.025) SERIES 12POSITION CAP HOUSING ASSEMBLY (PCB V-TYPE)

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Application Specification

Crimping Of 025 Receptacle Contact

TIF

Japanese

Crimping Of 025 Receptacle Contact

PDF

Japanese

Product Specification

025 SERIES I/O CONNECTORS (H-Type V-Type 2Row, Wire To Wire)

PDF

Japanese

025 SERIES I/O CONNECTORS (H-Type V-Type 2Row, Wire To Wire)

PDF

Japanese

0.64III SERIES CONNECTOR 2ROW

PDF

Japanese

0.64III SERIES CONNECTOR 2ROW

TIF

Japanese

Downloaded from Arrow.com.

0.64III SERIES CONNECTOR 2ROW

PDF

Japanese

.025 IDC Connectors

PDF

Japanese

.025 IDC Connectors

TIF

Japanese

.025 IDC Connectors

PDF

Japanese

.025 IDC Connectors

TIF

Japanese

Qualification Test Report

0.64III SERIES CONNECTOR 2ROW

PDF

Japanese

025 SERIES CONNECTOR (H-Type, V-Type, Wire To Wire)

PDF

English

Instruction Sheets

Instruction Sheet (non U.S.)

025 SERIES I/O CONNECTORS (H-Type, V-Type 2Row)

PDF

Japanese

FEATURES +

PRODUCT COMPLIANCE +

CALL US | LIVE CHAT | FULL SITE

Downloaded from Arrow.com.