

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	PRODUCTION ISSUE	05FEB2019	PNT	MT




TABLE 1: FOR -3,-4,-25

PART DESCRIPTION	H		J		P	S	T	U	JO	W
	MIN a	MAX b	MIN a	MAX b	±10% b	±10% b	±10% b	±10% b	±10% b	±20% b
242W042	<u>31</u> [1.22]	<u>17.9</u> [0.70]	<u>31</u> [1.22]	<u>7.0</u> [0.28]	<u>55</u> [2.17]	<u>35</u> [1.38]	<u>3.5</u> [0.14]	<u>2.0</u> [0.08]	<u>25</u> [0.98]	<u>1.8</u> [0.07]
242W053	<u>36</u> [1.42]	<u>22.1</u> [0.87]	<u>36</u> [1.42]	<u>8.4</u> [0.33]	<u>60</u> [2.36]	<u>40</u> [1.57]	<u>3.5</u> [0.14]	<u>2.0</u> [0.08]	<u>30</u> [1.18]	<u>2.0</u> [0.08]
242W063	<u>43</u> [1.69]	<u>27.9</u> [1.10]	<u>43</u> [1.69]	<u>9.9</u> [0.39]	<u>65</u> [2.56]	<u>45</u> [1.77]	<u>3.5</u> [0.14]	<u>2.0</u> [0.08]	<u>35</u> [1.38]	<u>2.2</u> [0.09]

TABLE 1: FOR -12,-100 MATERIAL


PART DESCRIPTION	H		J		P	S	T	U	JO	W
	MIN a	MAX b	MIN a	MAX b	±10% b	±10% b	±10% b	±10% b	±10% b	±20% b
242W042	<u>31</u> [1.22]	<u>17.9</u> [0.70]	<u>18</u> [0.71]	<u>7.0</u> [0.28]	<u>55</u> [2.17]	<u>35</u> [1.38]	<u>3.5</u> [0.14]	<u>2.0</u> [0.08]	<u>25</u> [0.98]	<u>1.8</u> [0.07]
242W053	<u>36</u> [1.42]	<u>22.1</u> [0.87]	<u>21</u> [0.83]	<u>8.4</u> [0.33]	<u>60</u> [2.36]	<u>40</u> [1.57]	<u>3.5</u> [0.14]	<u>2.0</u> [0.08]	<u>30</u> [1.18]	<u>2.0</u> [0.08]
242W063	<u>43</u> [1.69]	<u>27.9</u> [1.10]	<u>25</u> [0.98]	<u>9.9</u> [0.39]	<u>65</u> [2.56]	<u>45</u> [1.77]	<u>3.5</u> [0.14]	<u>2.0</u> [0.08]	<u>35</u> [1.38]	<u>2.2</u> [0.09]

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± -



DWN 05FEB2019

PRAVEEN N T

CHK 05FEB2019

N NAGAR

APVD 05FEB2019

M TAYLOR

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

MATERIAL

SEE SHEET 2

FINISH

-



TE Connectivity Ltd.

NAME

BOOT, 135 DEGREES WITH LIP

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-242W0XX-XX-0

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2

REV 3

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

COMPATABILITY CHART

ORDERING INFORMATION


NOTE

- DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0	PLC	$\pm$	—
1	PLC	$\pm$	—
2	PLC	$\pm$	—
3	PLC	$\pm$	—
4	PLC	$\pm$	—
ANGLES			



DWN	PRAVEEN N T	05FEB2019
CHK	N NAGAR	05FEB2019
APVD	M TAYLOR	05FEB2019

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

MATERIAL

SEE SHEET 2

FINISH



TE Connectivity Ltd.

NAME

BOOT, 135 DEGREES WITH LIP

SIZE
A4

CAGE CODE
00779

DRAWING NO
C- 242W0XX-XX-0

RESTRICTED TO

SCALE

DNS

SHEET

2 OF 2

REV 3