



Pushing Performance
Since 1945

HPP V4 cover aL IP65/67, w./o. cord



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 845 0015
Specification	HPP V4 cover aL IP65/67, w./o. cord
HARTING eCatalogue	https://harting.com/09458450015

Identification

Category	Accessories
Series	HARTING PushPull (V4)
Type of accessory	Protection cover
Description of the accessory	for connectors

Version

Details	Version with active locking without cord
---------	--

Technical characteristics

Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained



Pushing Performance
Since 1945

Specifications and approvals

Specifications	EN 45545-2
----------------	------------

Commercial data

Packaging size	100
Net weight	8.4 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140064690
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467