



Part Number : [1200700419](#)
Product Description : Micro-Change (M12) 5 Poles, 1/2" - 14 NPT Mounting Thread, Receptacle to 18 AWG PVC Leads, 0.5m (1.64') Length
Series Number : 120070
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : 8R5000A16M005




Documents & Resources

Drawings
[1200700419_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Triphenyl-phosphate per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120070
Description	Micro-Change (M12) 5 Poles, 1/2" - 14 NPT Mounting Thread, Receptacle to 18 AWG PVC Leads, 0.5m (1.64') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Micro-Change (M12)
Type	Single Ended (pigtail)
UPC	78172513382

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	0.50m
Material - Component	Nickel-plated Zinc Die-Cast
Mounting Thread Size	1/2" - 14 NPT
Net Weight	14.000/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1569
Wire Size (AWG)	18

This document was generated on Mar 08, 2025