



D-150-C-13 Product Details


[Share](#)


[Print](#)

[Email](#)


 **Active**

C-Wrap Side Entry Repair Sleeve

D-150-C-13

D-150-C-13 

TE Internal Number: CX2097-000

Product Highlights [View All](#)

- Heat Shrink Repair Sleeve
- Wire/Cable Size = 16 - 18 AWG
- Conductor Outer Diameter = 1.50 - 2.30 mm
- Adhesive Inside Diameter = 2.13 mm
- Sleeve Inside Diameter = 3.43 mm

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Heat Shrink Repair Sleeve
Color	Blue

Termination Features

Wire/Cable Size (AWG)	16 - 18
-----------------------	---------

Dimensions

Conductor Outer Diameter (mm [in])	1.50 - 2.30 [0.059 - 0.090]
Adhesive Inside Diameter (mm [in])	2.13 [0.084]
Sleeve Inside Diameter (mm [in])	3.43 [0.135]
Adhesive Cut Length (mm [in])	21.59 [0.85]
Sleeve Cut Length (mm [in])	19.05 [0.75]

Industry Standards

RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental

Operating Temperature (°C)	-65 - +150
----------------------------	------------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

