



Part Number : [1300940340](#)


Product Description : Standard Duty Support Grip, Offset Eye, Split Lace, Single Weave, Cable Diameter 38.10-44.20mm (1.500-1.740"), Approximate Break Strength 1179.34kg (2600 lbs)

Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Number : 35200



Documents & Resources

Drawings

[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Offset Eye, Split Lace, Single Weave, Cable Diameter 38.10-44.20mm (1.500-1.740"), Approximate Break Strength 1179.34kg (2600 lbs)
Product Name	Standard Duty
Type	Support Grip
UPC	78678835200

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	762.04kg (1680 lbs)
Bale Length	0.127m (5.00")
Body Style	Straight
Cable Diameter	38.10-44.20mm (1.500-1.740")
Color - Grommet	N/A
Eye Type	Offset
Gender	N/A
Material - Body	N/A
Material - Grip	Non-magnetic Tin Bronze Wire
Mesh Length	0.432m (17.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A