

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 13624362

☐ Compare

13624362 - Ground Strap Ring Female Unsealed Tin Plating Terminal, Cable Range 0.50 - 0.75 mm2

☐ Compare

Ground Strap Ring Female Unsealed Tin Plating Terminal, Cable Range 0.50 - 0.75 mm2



Part # 13624362

[Question about this product?](#)

Attributes

Documents (4)

Part # :	13624362
Description :	Ground Strap Ring Female Unsealed Tin Plating Terminal, Cable Range 0.50 - 0.75 mm2
Product Type :	Terminal
Status :	✓ Active
Terminal Family :	RING
Series :	GRD STRAP
Gender :	Female
Sealable :	Unsealed
Material :	CuZn30
Weight [g] :	2
Plating :	Tin
Minimum Cable Diameter [mm] :	1.40
Maximum Cable Diameter [mm] :	1.90
Minimum Cable Core Cross Section [mm2] :	0.50
Maximum Cable Core Cross Section [mm2] :	0.75
Remarks :	Stud Size: M6
RoHs compliant :	✓ Yes
ELV compliant :	✓ Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.