



+ CONNECTORS

RUGGEDIZED BACKSHELLS & ADAPTERS



✓ Active

TE CONNECTIVITY (TE)
TXR40AB90-1208AI2

Raychem | TCR , Terminator

TXR40AB90-1208AI2
TE Internal Number: 164883-000
Alias ID: 2-1191190-7

Not EU RoHS Compliant
Not EU ELV Compliant

Cable Diameter Range 6.4 – 10.2 mm [.25 – .4 in]
Connector General Specification Number MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W
Connector Detail Specification Number D38999/20, D38999/24, D38999/26, D38999/40, D38999/42, D38999/46, D38999/47
Material Aluminum
Adapter Plating Material Cadmium (AMS-QQ-P-416 Type II, Class 3)

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings
Tinel-Lock Adapter
PDF
English

CAD Files
3D PDF
PDF
3D
Customer View Model
2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

5-1654025-5_sec6_Adapters

PDF

English

Product Specifications

Product Specification

Braid Termination Using A Tinel Lock Ring Installed Using A Resistance Heater.

PDF

English

PERFORMANCE SPECIFICATION Tinel-Lock Rings, Heat Recoverable For Braid Termination

PDF

English

ASSEMBLY GUIDE For Tinel -Lock Rings, Heat Recoverable For Braid Temination

PDF

English

Adapter Finish Specifications

PDF

English

General Harness Repair Manual

PDF

English

General Information Package For Tinel-Lock Adapters

PDF

English

Product Environmental Compliance

REACH Substance Communication Document

RSCD_Cadmium

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Adapter Angle 90
Style Tinel-Lock Adapter
Termination Device Type Side-Entry Tinel-Lock Ring, Tinel-Lock Ring
Connector Shell Size 13, C
Accessory Type Tinel-Lock Adapter

Body Features

Color Olive Drab
Material Aluminum
Adapter Plating Material Cadmium (AMS-QQ-P-416 Type II, Class 3)
TE Adapter Code 40
Adapter Entry Size 8

Termination Features

Overbraid Termination Tinel-Lock Ring

Dimensions

Cable Diameter Range 6.4 – 10.2 mm [.25 – .4 in]
Cable Entry Diameter .2 – 12.7 mm [.01 – .5 in]

Usage Conditions

Operating Temperature Range -65 – 175 °C [-85 – 347 °F]
Salt Spray Resistance (Hr) 500

Industry Standards

Connector Detail Specification Number D38999/20, D38999/24, D38999/26, D38999/40, D38999/42, D38999/46, D38999/47

Other

Connector General Specification Number MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF