© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

WIRE AND CABLE

TWISTED PAIR CABLE



✔ Active

TE CONNECTIVITY (TE)

44A0131-16-3/6/9

Raychem | RC , SP

44A0131-16-3/6/9
TE Internal Number: 382409-000
Alias ID: 1192863-5

EU RoHS Compliant
EU ELV Compliant

Cable Type Spec 44

Voltage Rating (VAC) 600

Conductor Material Tin-Plated Copper

Wire Size (AWG) 16

Operating Temperature Range (°C) -65 – 150

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Three Conductor Cable, Unshielded, Unjacketed, General Purpose, 600 Volt
PDF
English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Polyalkene-Insulated, Copper Or Copper Alloy
PDF
English

FEATURES

Downloaded from Arrow.com.

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 44
Cable Style Primary
Product Type Cable
Product Classification Cable - High Performance - Spec 44, 55 and RCW

Configuration Features

Number of Strands 19
Number of Conductors 3

Electrical Characteristics

Voltage Rating (VAC) 600

Body Features

Conductor Material Tin-Plated Copper
Cable Configuration Three Conductor
Wire Color Blue, Orange, White

Dimensions

Strand Size (AWG) 29
Wire Size (AWG) 16
Overall Outside Diameter 3.96 mm [.156 in]

Usage Conditions

Operating Temperature Range (°C) -65 – 150

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.