






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/22/08	
A		REVISED SHAPE	10/24/11	
B		UPDATE SPEC.	11/8/16	AY/YC



POSITION=2~6



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Electrical:

Voltage Rating: 500V AC,DC

Current Rating: 8A AC,DC

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 1500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



A = .165 [4.20] X No. of Spaces

B = .165 [4.20] X No. of Positions+ .055 [1.40]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE MM [INCHES]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 Ø.X ± .10
 .XX ± .020 Ø.XX ± .015
 .XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	DY	9/22/08
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE FEMALE WIRE HOUSING, SINGLE ROW
 .165 [4.20] PITCH

SIZE X	PART NO. DMH-XX-S	REV. B
REF: S00016T	SCALE: NTS	SHEET 1 OF 1