



YAEV25-H2



Active

YAEV25-H2

Ring Tongue Terminal, 300 V, 0.83 IN W, 2.82 IN L, Nylon Insulation

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) | [Customer Drawing](#)

 [Email Datasheet](#)

 [Print Datasheet](#)

Specifications

Documents

Tools & Dies

DimensionalGeneralOther FeaturesOtherApprovals / CertificationsConductor(s)Physical

Dimensional	
Tongue Angle	Straight
Length (in)	2.82
Tongue Type	Ring
Stud Size (in)	5/16
Pad Width (in)	0.83
Strip Length	11/16
General	
Product Description	Ring Tongue Terminal, 300 V, 0.83 IN W, 2.82 IN L, Nylon Insulation
Other Features	
UPC	7818101137699
Other	
Installation Tooling	MY28-6Y35, Y39with U25ETDie Set
Approvals / Certifications	
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Conductor(s)	
Aircraft Cable Size (Range)	AN 0
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	1/0
Physical	
Type of Plating	Tin
Connector Type	Terminal
Color Code	Blue
Insulation Type	Nylon
Plated (Yes or No)	Y