






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/21/20	



Poles	Dimensions			
	A	B	C	D
06	.250 [6.35]	.550 [13.97]	.799 [20.30]	1.128 [28.65]
09	.500 [12.70]	.807 [20.50]	.807 [20.50]	1.130 [28.70]
12	.750 [19.05]	1.059 [26.90]	.807 [20.50]	1.134 [28.80]
15	1.000 [25.40]	1.311 [33.30]	.803 [20.40]	1.134 [28.80]

SPECIFICATIONS:

Material:
 Insulator: Nylon66, rated UL 94V-2
 Insulator color: Natural
 Electrical:

Current rating: 06~15P: 9 Amp max (With UL1007, 16AWG)
 Contact resistance: 20 mohms max
 Insulation resistance: 1,000 Mohms min
 Dielectric withstanding voltage: 2,900 VAC for 1 minute
 Temperature Rating:
 -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

ADAM TECH
 INTERCONNECTS
 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	LH	2/21/20
CHECKED	AT1	2/21/20
APPROVED		

TITLE .250 [6.35MM] PITCH CONNECTOR, HOUSINGS, FEMALE, VERTICAL		
SIZE X	PART NO. DME-F2-XX-SQ	REV. -
REF: S00124T	SCALE: NTS	SHEET 1 OF 1