

BU-32615-@

(Insulated Tip Jack)



- Mueller's BU-32615 is an insulated tip jack used for easy mounting.
- Recommended mounting hole of 3/16" (4.76mm)
- Overall length of 31/32" (24.6mm) and OD of 0.297" (7.54mm)
- Accepts pins of 0.08" +/- .001" (2.03mm +/- 0.025mm)
- Maximum Operating Temperature: 115°C (239°F)
- Material:
 - Contact – Tin plated Phosphorous Bronze
 - Insulation – Nylon
- Rating: 1 KV, Capacity of 4.0 pf
- Color: The "@" in the model number represents color. Available colors:
 - 8 Gray, -9 White
- RoHS 2 Compliant