







NOTES:

1. Electrical Char
 - Insulation Resistance: 500MΩ min. 500V DC for 1 minute
 - Contact Resistance: 30mΩ max.
 - Rating Current: 1.5A max.
 - Rating Voltage: 150V AC
 - Dielectric Voltage: 1000 Vrms at 1MA 60 sec. min.


2. Physical Char
 - Housing: PBT Glass filled (UL 94V-0) Color: Black
 - Soldering Temperature: 235°C for 5 sec.
 - Spring Wire: 0.45mm Dia Phosphor Bronze
 6u" Gold plating over Nickel
 - Temperature Range: -40°C to +85°C
 - Durability: 750 mating cycles min.

3. Packing: Tray





PCB LAYOUT
(TOP VIEW)



Detail A

RoHS compliant

Unit:mm

Scale	Free
TOLERANCE	
.XX	±0.20
.XXX	±0.13
.XXXX	±0.05
DIM	TOL
X.°	+0°30'
Angle	TOL

Id.	Modification	Date	Name
②	Correct dimension	14.02.2022	Daniel
①	Add dimension	09.12.2020	Daniel
⓪	Drawn	04.08.2016	Winnie

	Date	Name
Drawn	18.11.2020	Winnie
Approved	14.02.2022	Daniel

ASSMANN WSW components

Description: Modular jacks

ASSMANN WSW-No.
A-2004-2-4-LPS-N-R

Drawing-No.
ASS 7323 CO

rev02

Customer-No.

SHEET
1 / 1

Downloaded from Arrow.com.