
Part Number : 1731120335
Product Description : FCT Knurled Thumb Screw Lock with Plastic Head, #4-40 Thread, 45.30mm Length, Nickel-plated Brass
Series Number : 173112
Status : Active
Product Category : D-Sub Accessories
Engineering Part Number : FRSK1/5



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:cb1a3ceb-84e6-498c-a587-0c7521a08d09
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Accessories
Series	173112
Description	FCT Knurled Thumb Screw Lock with Plastic Head, #4-40 Thread, 45.30mm Length, Nickel-plated Brass
IP Rating	N/A
Magnetic	Yes
Product Name	FCT Products
Type	Backshell
UPC	191128075398

Physical

Accessory Type	Locking Mechanism
Material - Body	Brass
Net Weight	3.500/g
Packaging Type	Bag
Shell Size	1, 2, 3, 4, 5
Thread Size	4-40 UNC
Thread Type	Standard

Downloaded from Arrow.com.