

PPC-L127T

12.1" Fanless Panel PC with Intel® Celeron® M Processor



Features

- 12.1" TFT SVGA LCD with optional resistive touchscreen
- Embedded Intel® ULV Celeron® M 1 GHz
- System memory up to 1 GB DDR
- Window® CE 6.0 and XPe available
- Removable front bezel
- Fanless and ultra-low power consumption
- Automatic data flow control over RS-485 (COM2)
- Supports GPIO function (optional)

Introduction


The PPC-L127T is a panel computer designed without a fan, which makes it an ideal solution for low noise operating environments and clean room applications. PPC-L127T meets the VESA standard for mounting holes so that it can be used in many different kinds of installations. The front bezel can be removed to make maintenance of the LCD and touchscreen easier and quicker. The support for one CompactFlash disk also makes system maintenance more convenient.

Specifications

Processor System	CPU	Embedded Intel ULV Celeron M 1.0 GHz
	Secondary Cache	None
	Memory	1 x 184-pin DIMM sockets, supporting DDR200/266 modules for up to 1 GB
	Combo Drive	Optional 989KL12710E
	SSD	1 x type II CompactFlash socket, built-in 128 MB CF card in PPC-L127T-CE-RTE.
	HDD	1 x internal IDE interface, 2.5" type
	Network (LAN)	10/100 Mbps Ethernet
	Fully Integrated I/O and Speakers	- 4 x serial ports: RS-232 x 3, RS-232/422/485 x 1 - 1 x parallel port - 6 x USB ports (4 x external, 2 x internal) - 1 x PS/2 mouse and keyboard - Mic-in, Line-in, Line-out - 1 x VGA port - 2 x 1.3 W speakers - 8-bit GPIO through COM3 (Optional)
	Bus Expansion	1 x expansion slot for PCI/ISA card 1 x MINI PCI expansion slot
	Front Panel Protection	IP65/NEMA 4 compliant
Weight		3.25 kg (7.151 lb)
Dimensions (W x H x D)		340.5 x 269.3 x 70.5 mm (13.41" x 10.6" x 2.78")
OS Support	Microsoft Windows XPe, CE, XP Pro, 2000	
Supply	Input Voltage	12 ~ 25 V DC, 4.5 A max; 15 ~ 25 V DC with Battery Pack
LCD Display	Display Type	12.1" TFT LCD
	Max. Resolution	800 x 600 , Optional 1024 x 768
	Colors	262 K
	Dot Size (mm)	0.3075 x 0.3075
	Viewing Angle	70° (left), 70° (right), 60° (up), 50° (down)
	Luminance	400 cd/m ²
	Operating Temperature	-30 ~ 85° C
	Brightness Control	Yes
Touchscreen (Optional)	Backlight Lifetime	50,000 hours (min)
	Type	Analog Resistive (5 wires) (Resistive with Sunlight Readable as an option))
	Resolution	Continuous
	Light Transmission	80%
	Controller	USB interface
	Power Consumption	< 5 V @ 60 mA
	Software Driver	Supports Windows NT/98/2000/ME/XP
Durability (Touches)		35 million

Dimensions

Unit: mm



Specifications

Environmental Specifications	Operating Temperature	0-50° C (32-112° F)
	Storage Temperature	-20 ~ 60° C
	Relative Humidity	10 ~ 95% @ 40° C (non-condensing)
	Shock	10 G peak acceleration (11 msec. duration)
	EMC	BSMI, CE, FCC Class B
	Safety	CB, CCC, BSMI, UL
	Vibration	1 G


Ordering Information

Part No.	Description
PPC-L127T-080-XE	Intel ULV Celeron M only for processor-based Fanless Panel Computer with 12.1" TFT LCD
PPC-L127T-R80-XE	PPC-L127T-080 with Resistive Touch screen
PPC-L127T-CE-RTE	PPC-L127T with Windows CE.Net 6.0 on 128 MB CompactFlash

Accessories

Part No.	Description
PPC-ARM-A03	VESA standard ARM for PPC series
PPC-EXP-L127E	PCI/ISA Expansion kit for PPC-L127T
PPC-L126 WL-MT	Wall Mount Kit for PPC-L126T
PPC-L126Rack-MT	19" Rack Mounting Kit for PPC-L126
PS-DC19-L61E	19V DC power adapter module for PPC-L61E/L127
989KL12710E	Combo ASS'Y Kit for PPC-L127T
989KL12711E	CD-ROM ASS'Y Kit for PPC-L127T
989KL12709E	Wireless LAN Module for PPC-L127T
989KL12712E	DVD-RW ASS'Y for PPC-L127T
1702002600	Power Cord 3P UL/CSA(USA) 125V 10A 1.83M 180D
1702002605	Power cord 2P FRANCE 10A/16A 220V 1.83M 90D

Fully-Integrated I/O



- A. Main power switch
- B. USB 2.0 x 4
- C. Ethernet jack
- D. PS/2 mouse and keyboard
- E. VGA port
- F. PCI/ISA expansion slot cover
- G. DC inlet
- H. Line-in jack
- I. Line-out jack
- J. Mic-in jack
- K. Parallel port
- L. Serial ports
- M. Battery door cover

