Part Number : 190670041
Product Description : NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Carton
Series Number : 19067
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : D-956-14



Documents and Resources

Drawings

190670041_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-013-001.pdf

PS-19902-016-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	NylaKrimp
Style	Ring
Type	Ring Terminal
UPC	800753065864

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	3.057/g

Downloaded from Arrow.com.

Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/4" (M6)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	8.98mm max.
Wire Size (AWG)	8

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	640013900
Crimp Tool Kit for 8 AWG Insulated Ring Terminals	640017670

Downloaded from Arrow.com.