



1969590-5 Product Details

[Share](#) | [Print](#) | [Email](#)


Economy Power Connectors

HSG, REC, PANEL MOUNT, SINGLE ROW, EP2.5

1969590-5

TE Internal Number: 1969590-5

Active
 [View 3D PDF](#)

Product Highlights [View All](#)

- Economy Power 2.5 Product Line
- Connector
- Wire-to-Wire, Wire-to-Panel
- Applies To Wire/Cable
- 5 Positions

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Line	Economy Power 2.5
Product Type [?]	Connector
Connector Type	Housing
Sealed	No

Mechanical Attachment

Mating Retention Type	Latch(ing)
-----------------------	------------

Electrical Characteristics

Contact - Rated Current (A)	7.5
Operating Voltage Reference	AC
Operating Voltage (VAC)	250

Termination Features

Wire/Cable Size (AWG)	22 - 26
Wire/Cable Size (mm ²)	0.13 - 0.33
Termination Method to Wire/Cable	Crimp

Dimensions

Length (X-Axis) (mm [in])	15.00 [0.591]
Width (Z-Axis) (mm [in])	18.17 [0.715]
Profile Height (Y-Axis) (mm [in])	6.60 [0.260]

Body Features

Mating Retention	With
------------------	------

Contact Features

Contact Type	Pin
--------------	-----

Housing Features

Centerline (mm [in]) [?]	2.50 [0.098]
Connector Style	Receptacle
Housing Color	White
Housing Material	Nylon - GF

Configuration Features

Number of Positions [?]	5
Number of Rows	1

Industry Standards

RoHS/ELV Compliance [?]	Not reviewed for ELV/RoHS compliance
Lead Free Solder Processes [?]	Not reviewed for lead free solder process
UL Flammability Rating	UL 94V-0

Environmental

Operating Temperature (°C [°F])	-25 - +105 [-13 - +221]
---------------------------------	-------------------------

Conditions for Usage

Applies To	Wire/Cable
Glow Wire Rating	Standard Part - Not Glow Wire
Accepts Wire Insulation Diameter, Range (mm [in])	1.30 - 1.70 [0.051 - 0.067]

Operation/Application

Application Use	Wire-to-Wire, Wire-to-Panel
Contact Transmits (Typical Application)	Power

Packaging Features

Packaging Method	Bag/Box
------------------	---------

Other

Brand	TE Connectivity
Comment	Panel Mount

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

