Part Number : 1300910028
Product Description : Woodhead Standard Duty Reel, 16/3 SJTOW Cord, 15.24m (50.0') Cord Length with 13W Fluorescent Hand Lamp and Handle Ballast
Series Number : 130091
Status : Active
Product Category : Electrical Reels
Engineering Part Number : 980-86



Documents and Resources

Drawings

1300910028_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Electrical Reels
Series	130091
Description	Woodhead Standard Duty Reel, 16/3 SJTOW Cord, 15.24m (50.0') Cord Length with 13W Fluorescent Hand Lamp and Handle Ballast
Enclosure Rating	NEMA 1
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678833610

Agency

UL	E22769

Electrical

Current - Maximum per Contact	8.0A
GFCI	No
Lamp Wattage - Maximum	13W
On/Off Switch	Yes
Voltage - Maximum	120V

Physical

Bulb Included	Yes
Cable Length	0.457m (1.50')
Cable Movement	Ratchet Lock
Cord Length	15.24m (50.0')
Cord Type	16/3 SJTOW
Depth	0.30m (11.75")

Downloaded from Arrow.com.

Drum Lock	Ratchet
Duty	Standard
Guide Arm	2 - Position
Height	0.36m (14.25")
Lamp Type	Fluorescent
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Width	196.85mm (7.750")
Wire Size (AWG)	16

Downloaded from Arrow.com.