



[Back to Result](#)



S100X225VATY

[Add to BOM](#) | [Add to Favorites](#)

White print-on area, vinyl label for 8 – 4 AWG wires, Cat. 6AUTP, FTP/Cat. 6 FTP cable.

Product Details	Related Documents
Std. Pkg. Qty.	5000
Std. Ctn. Volume (cf)	0.7051
Std. Pallet Weight (lb)	1,320.0000
Std. Pallet Volume (cf)	42.304688
Std. Ctn. Weight (lb)	22.0000
RoHS Compliancy Status	Compliant
Note	S100X225VATY replaces TTSL3523VC3-1 , TTSL4PO3-5 , TTSL4VC3-5 , TTSL56TC3-1 and TTSL6626VC3-5
Part Description	White print-on area, vinyl label for 8 – 4 AWG wires, Cat. 6AUTP, FTP/Cat. 6 FTP cable.
Material	Vinyl
Length (mm)	57.2
Width (mm)	25.4
Width (In.)	1.00
Length (In.)	2.25
No. of Fibers	24
Print-On Area Color	White
Max. Wire O.D. (mm)	12.1
Max. Wire O.D. (In.)	0.48
Labels Per Row	4
Min. Cable O.D. (mm)	6.1
Min. Cable O.D. (In.)	0.24
Wire Range	Cat. 6 FTP / Cat. 6a (10 Gig) UTP / Cat. 6e (10 Gig) FTP / 8 - 4 AWG
Pricing Description	ThermTrans, Self-Lam Label, Vinyl, 1.00" Wx2.25" H, .75" POA, Clear/White, 3" core
BMEcat - Model	Adhesive label, Roller shape
Print-On Area Height (In.)	0.75
Printer	Thermal Transfer
Labels Per Roll	4
Label Type	Thermal transfer self-laminating
Print-On Area Height (mm)	19.1
BMEcat - with text field	True
Min. Order Qty.	5,000.0000