



A



- | | | | | | | |
|---|----------|---------------------|--------|---------------------|------------------------|--|
| 9 | OBSOLETE | | | | | |
| | GREEN | NO | YELLOW | NO | 5-6605301-7 | |
| | GREEN | NO | GREEN | NO | 5-6605301-7 | |
| | GREEN | YES | YELLOW | YES | 5-6605301-1 | |
| | LED1 | 250 OHMS RESISTOR 5 | LED2 | 250 OHMS RESISTOR 5 | PART NUMBER | |

THIS DRAWING IS A CONTROLLED DOCUMENT.		P/N G. ATTADIA Q/E D. FAROLE A/P/V D. FAROLE	04MAR2005 DOCK5 04MAR2005 04MAR2005	 TRP connector Dongguan China	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-2100 APPLICATION SPEC —	NAME 1X1 MAG45(TM), 4N2P10 10/100 ETHERNET SCHEMATIC, 314P10 MAGNETIC CIRCUIT, SHIELDED, DECOUPLING CAPACITOR, WITH LEADS	SIZE CASE CODE C-6605301	RESTRICTED TO
	0 PLC ± — 1 PLC ± .010 2 PLC ± .005 3 PLC ± .005 4 INCHES ± — ANGLES ± —	WEIGHT —	CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 1
MATERIAL 	FINISH 			REV F	