






Loading-Plan:



- 1 brown
- 2 blue
- 3 white
- 4 green
- 5 pink
- 6 yellow
- 7 black
- 8 grey
- 9 red
- 10 violet
- 11 grey-pink
- 12 red-blue



4.0 to 100	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

Part no.	21348700CXXXXXX
----------	-----------------

Type of cable	XX
PVC grey, 12x0.14mm²	XX=79
PUR black, 12x0.14mm²	XX=78

- Protection level: IP67
- Temperature range: -30°C ... +80°C

All rights reserved
Department EC PD - RO
HARTING Electronics GmbH
D-32339 Espelkamp

All Dimensions in mm
Original Size DIN A3

Scale
2:1

Free size tol.

Created by
TAMAS

Inspected by
STOICA

Standardisation
HOFFMANN

Date
2014-08-25

State
Final Release

Title
M12 A-coded Cable Assembly

Type
TB

Number
21348700CXXXXXX

Doc-Key / ECM-Nr.
100591310/UGD/009/A
500000079105

Rev.
A

Page
1/1