



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

To obtain a copy of the owner's manual for your B022-U08-IP or B022-U16-IP KVM, please contact Product/Technical Support – (773) 869-1234. You will need to have the serial number for your product at the time of the call. Should you experience any inconsistencies in upgrading firmware or lengthy load times, please contact the Product/Tech Support team at Tripp Lite.

NetDirector 8-Port 1U Rack-Mount IP KVM Switch

MODEL NUMBER: **B022-U08-IP**



Description

The B022-U08-IP NetDirector IP KVM Switch allows secure access to multiple computers from a single KVM (keyboard, monitor and mouse) console. A single KVM can directly control up to 8 computers. Daisy-chain up to 31 additional B022-U08 switches to control up to 256 computers.

Built-in IP access allows the B022-U08-IP to be accessed from any computer on the LAN, WAN or Internet, whether that computer is located down the hall or halfway around the world. Simply log on via web browser using the Windows- and Java-based browser clients; or, access the KVM without a browser using the included Windows- and Java-based non-browser applications. Remote authentication is also supported via RADIUS and LDAP/S.

A full-screen graphical OSD with multi-level authentication (Super Administrator, Administrator and User) allows you to quickly and efficiently manage your installation, and can be displayed in English, Spanish, French, German, and Japanese. Critical events on the installation can be tracked via the Log in the web interface, or the included Windows-based Log Server can be installed for more robust tracking.

Once a remote session is initiated, you will be able to control the connected computers as if they were physically connected to your keyboard, monitor, and mouse. You can manually switch between computers using keyboard hotkeys, the remote session toolbar, or the KVM's OSD interface; or, you can automatically scan through each port using Auto Scan or Panel Array modes.

Constructed of heavy-duty steel housing. The B022-U08-IP includes two 6-ft Tripp Lite USB/PS2 combo KVM cable kits. All other cable kits can be ordered separately.

Features

Highlights

- Directly control up to 8 computers on a single KVM switch or up to 256 computers as part of a daisy-chain
- Remotely access computers via LAN, WAN or Internet via the Windows or Java browser clients
- Supports both IPv4 and IPv6
- Supports RADIUS and LDAP/S authentication
- 3-level security (Admin, User and Select) – up to 64 accounts can be created
- Compatible with all major operating systems

System Requirements

External Console

- A VGA, SVGA or MultiSync monitor capable of displaying the highest resolution provided by any computer in the installation.
- PS/2 or USB keyboard and mouse.

Computers

- A VGA, SVGA or MultiSync video graphics card with an HD15 port.
- Either a PS/2 or USB keyboard/mouse ports.
- Compatible with all major operating systems.

Remote Console

- For best results, computers that



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- 1U Rackmount KVM Switch with built-in IP access.
- Connect either USB or PS/2 computers using P778-Series USB/PS2 Combo KVM Cable Kits – no need for separate cable kits.
- Control up to 8 computers on a single KVM switch.
- Daisy-chain up to 31 additional B022-U08 switches to control up to 256 computers.
- Remotely access computers via LAN, WAN or Internet via the Windows™ or Java browser clients.
- AP Windows and Java non-browser applications allow the KVM to be remotely accessed via the network without going through a browser.
- External USB 1.1 port allows USB peripheral devices to be shared amongst connected computers.
- Grayscale feature allows you to view remote sessions in black and white, reducing the amount of data traveling over the network and improving keyboard/mouse response time over IP.
- Web management interface, OSD and toolbars provide convenient, user-friendly operation.
- 3-level security (Admin, User and Select) – up to 64 accounts can be created.
- Panel Array Mode – remotely monitor multiple ports at the same time.
- Message board feature allows users who are logged in at the same time to communicate with each other and manage port access.
- CD includes a Windows-based log server that records events on the installation and writes them to a searchable database.
- Supports RADIUS and LDAP/S authentication.
- Flash firmware upgradable via network and included firmware upgrade cable.
- Supports both IPv4 and IPv6.
- Supports Link Local IPv6 Address and IPv6 Stateless Auto configuration protocol.
- Web Management Interface, Remote OSD and Local OSD can be displayed in English, Spanish, French, German and Japanese.
- Advanced encryption technologies: 128-bit SSL, 128-bit RC4, 1024-bit RSA, 56-bit DES, 256-bit AES, 168-bit 3DES.
- Video resolutions up to 2048 x 1536, DDC2B are supported at the local console. Video resolutions up to 1600 x 1200 @ 60Hz, 24-bit color depth are supported at the remote console.
- Compatible with all major operating systems.

remotely access the KVM switch should have at least a Pentium III 1GHz processor.

- Users who want to access the KVM switch with the Windows client must have DirectX 8.0 or higher installed. DirectX is available for free download from Microsoft's website.
- Users who want to access the KVM switch with the Java client must have Sun's Java 6 (update 3 or higher) runtime environment installed. Java is available for free download from the Java website.
- For best results, a network transfer speed of at least 128Kbps is recommended.
- Browsers must support 128-bit data encryption.
- To run the Log Server, you must have the Microsoft Jet OLEDB 4.0 (or higher) driver installed.

Supported Web Browsers

- Internet Explorer 6 and higher
- Firefox 1.5 and higher
- Mozilla 1.7 and higher
- Safari 4.0 and higher
- Opera 9.0 and higher
- Netscape 8.1 and higher

Package Includes

- B022-U08-IP IP KVM Switch
- (x2) 6 ft. USB/PS2 Combo KVM Cable Kits
- USB/PS2 Combo Console Cable Kit



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- RJ11 to DB9 Firmware Upgrade Cable
- Rackmount Hardware
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A Output: 5.3V, 2.4A)
- Rubber Feet
- CD with Owner's Manual and Device Files
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332177049
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A / Output: 5.3V, 2.4A
Max CPU	8
PHYSICAL	
Housing Color	Black
Shipping Dimensions (hwd / cm)	23.11 x 54.36 x 11.68
Shipping Dimensions (hwd / in.)	9.10 x 21.40 x 4.60
Shipping Weight (kg)	3.54
Shipping Weight (lbs.)	7.80
Unit Dimensions (hwd / cm)	4.39 x 43.18 x 15.24
Unit Dimensions (hwd / in.)	1.73 x 17 x 6
Unit Weight (kg)	2.77
Unit Weight (lbs.)	6.1
ENVIRONMENTAL	
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	0 to 80% RH, Non-Condensing
Operating Temperature	0 to 50 C (32 to 122 F)
COMMUNICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	Yes
CONNECTIONS	
Ports	8
PC/Server Connections	PS/2; USB; VGA
FEATURES & SPECIFICATIONS	
Autoscan (Y,N)	Y
Autoscan Duration	1-255 Seconds
Number of Users	1
NIAP-Certified Secure	No
Cat5 KVM Switch	No
Technology	PS/2; USB; VGA/SVGA
STANDARDS & COMPLIANCE	
Approvals	CE, FCC, RoHS, External Power Supply Certified to UL
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>