


# Customer Information Sheet

| DRAWING No.: M80-4D1XXXXFC | SHT 2 OF 2 | IF IN DOUBT - ASK | © | NOT TO SCALE | THIRD ANGLE PROJECTION | ALL DIMENSIONS IN mm |
|---|---|---|---|---|---|---|





SECTION X-X




SECTION Z-Z



SPECIFICATIONS:
MATERIAL:
MOULDING = GLASS-FILLED PPS, UL94V-0, BLACK
ENVIRONMENTAL:
TEMPERATURE RANGE = -55°C TO +125°C
PACKING:
BAG
FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C005XX (LATEST ISSUE)

| DIMENSION | CALCULATION |
|---|---|
| DIM 'A' | TOTAL No. OF POSITIONS - 2 |
| DIM 'B' | TOTAL No. OF POSITIONS + 5 |
| DIM 'C' | TOTAL NUMBER POSITIONS + 10 |

EXAMPLE ORDER CODE: HOUSING WITH 20 POSITIONS AND FIXINGS

**M80-4182098**

DIM 'A' = 18.00mm, DIM 'B' = 25.00mm, DIM 'C' = 30.00mm.

NOTES:
1. HOUSING TO BE USED WITH M80-2060005 CONTACTS. CONTACTS SOLD SEPERATELY.
2. FOR ASSEMBLY INSTRUCTIONS, SEE IS-25.
3. LENGTH WILL BE 1.9 WHEN 101LOK SCREWS ARE ENGAGED WITH RETAINERS IN MATING CONNECTOR.

ORDER CODE:

**M80-418XX98**

TOTAL No. OF POSITIONS
04 TO 50
(EVEN NUMBERS ONLY)

| NAME | ISS. | DATE | C/NOTE |
|---|---|---|---|
| MSP | 1 | 10.04.17 | ----- |
| APPROVED: M.PERREN | | | |
| CHECKED: S.FLOWER | | | |
| DRAWN: M.PERREN | | | |
| CUSTOMER REF.: | | | |
| ASSEMBLY DRG: | | | |

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL: SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE: FEMALE T-CONTACT J-TEK CRIMP CONNECTOR WITH 101LOK JACKSCREWS

DRAWING NUMBER: **M80-418XX98**

SHT 2 OF 2