

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Protecting Covers

General Information

Extended Product Type:	PL6
Product ID:	1SNK900619R0000
EAN:	3472599097506
Catalog Description:	PL6 Protecting Cover - Transparent
Long Description:	- Prohibit access to the screw clamps, - Indicate live circuits.

Ordering

Color:	Transparent
Minimum Order Quantity:	10 piece
Customs Tariff Number:	39269097

Popular Downloads

Data Sheet, Technical Information:	1SNK160021D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	6 mm
Product Net Height:	49.2 mm
Product Net Length:	25.05 mm
Product Net Depth / Length:	25.1 mm
Product Net Weight:	1.8 g

Technical

Spacing:	6 mm
Function:	Protecting Covers
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polycarbonate
Recommended Screw Driver:	4 mm
Suitable For:	ZS6 ZS6-S

Technical UL/CSA

Flammability According to UL94:	V2
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230500F0202

Classifications

Object Classification Code:	X
E-nummer:	2925167

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	158 mm
Package Level 1 Depth / Length:	243 mm
Package Level 1 Gross Weight:	0.018 kg
Package Level 1 EAN:	3472599097506
Package Level 2 Units:	1500 piece
Package Level 3 Units:	72000 piece
Product Packing Type:	Bag

