Part Number : 1300940516
Product Description : Bus-Drop Support Grip, Locking Bale, Cable Diameter 13.21-18.54mm (.520-.730"), Approximate Break Strength 358.34kg (790 lbs)
Series Number : 130094
Status : Not Recommended For New Design
Product Category : Cable Grips
Engineering Part Number : 36586



Documents and Resources

Drawings

PK-130227-004-001.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Not Recommended For New Design
Category	Cable Grips
Series	130094
Description	Bus-Drop Support Grip, Locking Bale, Cable Diameter 13.21-18.54mm (.520-.730"), Approximate Break Strength 358.34kg (790 lbs)
Product Name	Service-Drop
Type	Support Grip
UPC	78678835814

Agency

CSA	LR32159

Physical

Approximate Break Strength	358.34kg (790 lbs)
Bale Length	0.356m (14.00")
Body Style	Straight
Cable Diameter	13.21-18.54mm (.520-.730")
Color - Grommet	N/A
Eye Type	Locking Bale
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.203m (8.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Downloaded from Arrow.com.