



Part Number : [08560124](#)

Product Description : KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Gold(Au)

Series Number : 7258

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 7258-A(P558)L

Packaging Alternative : [08560123](#) (Reel)



Documents and Resources

Drawings

[008560124_sd.pdf](#)

[PK-2759-001-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-40-02-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	7258
Description	KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Gold(Au)
Application	Power, Wire-to-Board
Product Name	KK,Trifurcon
UPC	800754226677

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.159/g
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	0.051µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size (AWG)	22, 24, 26
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	<u>11030016</u>
PremiumGrade Hand Crimp Tool for KK 3.96mm Terminals, 26-22 AWG	<u>638117400</u>

This document was generated on May 26, 2026