

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

Accessory

Middle Size

Mini Size

Large Size

Standard Size

M Series >

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



CC-02PMFS-QC800P

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL2238, UL50e

You must login first for view the price

Quantity - 1 +

 Check Stock

 Add to Cart


 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories


Connector Type ▼ Search



X-Lok, Accessory...
AB-CC-020202...
-20°C ~ +85°C

- 0 +


☐



X-Lok, Middle Siz...
AB-CC02BL-CCBL...
-20°C ~ +105°C

- 0 +


☐



X-Lok, Middle Siz...
AB-CC02BL-CCBL...
-20°C ~ +105°C

- 0 +


☐



X-Lok, Middle Siz...
AB-CC02BL-CCBL...
-20°C ~ +105°C

- 0 +


☐



X-Lok, Middle Siz...
AB-CC02BL-CCBL...
-20°C ~ +105°C

- 0 +

☐



X-Lok, Middle Siz...
AB-CC02BL-CCBL...
-20°C ~ +105°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 20A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 02
Connector Gender Male	Backshell Circular
Mating Style Push Lock	IP Rating IP68
Assembly Style Solder	
➕ More Options	

People Also Bought



CC-02PMFS-QC800P



AB-CB008FR-CB0H...



MSAS-12PFFS-...



MSAP-04BMMM-...



1B0-06BFFM-LL7A04