

© 2025 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	ECR-19-012652	21SEP2019	BS	CW
	C	ECR-21-105887	26JUL2021	BS	CW
	D	ECR-22-150866	13SEP2022	DL	CW
	E	ECR-25-237606	30MAY2025	ABS	RB







TYPE-1:T2030422201-000 TE LOGO
类 型-1:T2030422201-000 TE LOGO


M4 SCREW RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝，推荐锁紧力矩1.2Nm








4 X M3 SCREW RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝，推荐锁紧力矩0.5Nm





PANEL CUT OUT FOR INSERTS FOR USING
WITHOUT HOODS/HOUSINGS
不使用防护外壳时芯件的安装开孔图

NOTES:
1. TECHNICAL CHARACTERISTICS:
   INSULATION MATERIAL: PC
   RATED VOLTAGE: 250 V
   RATED CURRENT: 10 A
   INSULATION RESISTANCE: >=400MΩ
   RATED IMPULSE VOLTAGE: 4 KV
   POLLUTION DEGREE: 3
   FLAMMABILITY: UL94V-0
   MATING CYCLES: 500 CYCLES
   WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
   CONTACT TYPE: CRIMP CONTACT
2. CONTACT NEED TO BE ORDERED SEPARATELY.
   (ORDER No. REFER TO DRAWING: T20200X20XX000)

注释：
1. 技术参数：
   绝缘材料： PC
   额定电压： 250V
   额定电流： 10A
   绝缘电阻： >=400MΩ
   额定脉冲电压： 4 KV
   污染等级： 3
   阻燃等级： UL94V-0
   插拔次数： 500次
   接线范围： 0.14-2.5 mm² (26-14 AWG)
   接线类型： 冷压接
2. 端子需要单独订购，
   （订货号参考图面： T20200X20XX000）

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-
MATERIAL - -	FINISH - -

DWN	DAVID LI 18MAR2015
CHK	CHRIS WANG 18MAR2015
APVD	XU XIANG 18MAR2015
PRODUCT SPEC	108-137043
APPLICATION SPEC	114-137043
WEIGHT	-

TE Connectivity

NAME HDD-042-F

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	C-T2030422201000	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 2 | REV E

1470-19 (3/13)

Downloaded from Arrow.com.


© 2025 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


NOTES:


SEE SHEET 1


注释：
见页 1












TYPE-2:T2030422201-001 STAINLESS STEEL SCREW,NO LOGO
类 型-2:T2030422201-001 不锈钢螺丝,无LOGO

ALL DIMENSIONS ARE SAME AS TYPE 1,
EXCEPT THOSE DEFINED IN THIS TYPE.
除了在本类型中定义的尺寸外,其它尺寸同类型1



PART NUMBER 料号	PART DESCRIPTION 描述		TYPE 类型
T2030422201-001	HDD-042-F	HDD-042 FEMALE INSERT, CRIMPING SPLIT TYPE, STAINLESS STEEL SCREW,NO LOGO HDD-042冷压针分体式母插,不锈钢螺丝,无LOGO	TYPE-2 类 型-2
T2030422201-000	HDD-042-F	HDD-042 FEMALE INSERT, CRIMPING SPLIT TYPE HDD-042冷压针分体式母插	TYPE-1 类 型-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL - / -

FINISH - / -

DWN DAVID LI 18MAR2015
CHK CHRIS WANG 18MAR2015
APVD XU XIANG 18MAR2015
PRODUCT SPEC 108-137043
APPLICATION SPEC 114-137043
WEIGHT -

TE Connectivity

NAME HDD-042-F

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	C-T2030422201000	-

CUSTOMER DRAWING

SCALE 1:1 SHEET 2 OF 2 REV E

1470-19 (3/13)

Downloaded from Arrow.com.