Selection and ordering data

Diameter 70 mm, thermoplastic enclosure, degree of protection IP 65

	Version	Color	8WD44 signal. columns Order No.	List Price $ 1 unit	8WD44 signal. columns Order No.	List Price $ 1 unit	8WD44 signal. columns Order No.	List Price $ 1 unit	Weight approx. kg
	Lamp: Base BA 15d, 5 W, 24 V/ 115 V/230 V (not included in the scope of supply)								
8WD44 00-1A. 	• Steady-light element		Rated voltage UC 12 to 230 V						0.1
		red	**8WD44 00-1AB**	**49.00**					
		green	**8WD44 00-1AC**	**49.00**					
		yellow	**8WD44 00-1AD**	**49.00**					
		clear	**8WD44 00-1AE**	**49.00**					
		blue	**8WD44 00-1AF**	**49.00**					
			Rated voltage UC 24 V		Rated voltage AC 115 V		Rated voltage AC 230V		
	• Repeated-flash light element	red	**8WD44 20-1BB**	**113.00**	**8WD44 40-1BB**	**113.00**	**8WD44 50-1BB**	**113.00**	0.1
		green	**8WD44 20-1BC**	**113.00**	**8WD44 40-1BC**	**113.00**	**8WD44 50-1BC**	**113.00**	
		yellow	**8WD44 20-1BD**	**113.00**	**8WD44 40-1BD**	**113.00**	**8WD44 50-1BD**	**113.00**	
		clear	**8WD44 20-1BE**	**113.00**	**8WD44 40-1BE**	**113.00**	**8WD44 50-1BE**	**113.00**	
		blue	**8WD44 20-1BF**	**113.00**	**8WD44 40-1BF**	**113.00**	**8WD44 50-1BF**	**113.00**	
	• Single-flash light element with built-in electronic flash (no additional lamp or LED necessary)	red	**8WD44 20-0CB**	**200.00**	**8WD44 40-0CB**	**200.00**	**8WD44 50-0CB**	**200.00**	0.1
		green	**8WD44 20-0CC**	**200.00**	**8WD44 40-0CC**	**200.00**	**8WD44 50-0CC**	**200.00**	
		yellow	**8WD44 20-0CD**	**200.00**	**8WD44 40-0CD**	**200.00**	**8WD44 50-0CD**	**200.00**	
		clear	**8WD44 20-0CE**	**200.00**	**8WD44 40-0CE**	**200.00**	**8WD44 50-0CE**	**200.00**	
		blue	**8WD44 20-0CF**	**200.00**	**8WD44 40-0CF**	**200.00**	**8WD44 50-0CF**	**200.00**	
	LED version (integrated version)								
8WD44 20-5AB 	• Steady-light element LED	red	**8WD44 20-5AB**	**160.00**	**8WD44 40-5AB**	**160.00**	**8WD44 50-5AB**	**160.00**	0.1
		green	**8WD44 20-5AC**	**160.00**	**8WD44 40-5AC**	**160.00**	**8WD44 50-5AC**	**160.00**	
		yellow	**8WD44 20-5AD**	**160.00**	**8WD44 40-5AD**	**160.00**	**8WD44 50-5AD**	**160.00**	
		clear	**8WD44 20-5AE**	**160.00**	**8WD44 40-5AE**	**160.00**	**8WD44 50-5AE**	**160.00**	
		blue	**8WD44 20-5AF**	**160.00**	**8WD44 40-5AF**	**160.00**	**8WD44 50-5AF**	**160.00**	
	• Repeated-flash light element LED	red	**8WD44 20-5BB**	**175.00**	–		–		
		green	**8WD44 20-5BC**	**175.00**	–		–		
		yellow	**8WD44 20-5BD**	**175.00**	–		–		
	• Rotating-beacon element LED	red	**8WD44 20-5DB**	**193.00**	–		–		
		green	**8WD44 20-5DC**	**193.00**	–		–		
		yellow	**8WD44 20-5DD**	**193.00**	–		–		
	Acoustic elements				Rated voltage UC 115 V				
8WD44 20-0FA 	• Buzzer element [1] 85 dB Tone adjustable: pulsating or continuous		**8WD44 20-0FA**	**200.00**	**8WD44 40-0FA**	**200.00**	**8WD44 50-0FA**	**200.00**	0.1
	• Siren element [1]		Rated voltage DC 24 V						
	- 108 dB, IP 40		**8WD44 20-0EA**	**100.00**	–		–		0.1
	- Multi-tone siren, 100 dB, 8 tones and amplification can be set		**8WD44 20-0EA2**	**160.00**	**8WD44 40-0EA2**	**160.00**	**8WD44 50-0EA2**	**160.00**	0.1
	Connection element incl. cover								
8WD44 08-0AA, 8WD44 08-0AD 	• Screw terminals								0.1
	- for mounting on pipes		**8WD44 08-0AA**	**49.00**					
	- for mounting on bracket or floor		**8WD44 08-0AB**	**49.00**					
	• With Cage Clamp								
	- for mounting on pipes		**8WD44 08-0AD**	**49.00**					0.1
	- for mounting on bracket or floor		**8WD44 08-0AE**	**49.00**					

1) Operation necessitate top position mounting on column.

Downloaded from Arrow.com.

Accessories

	Design		Rated voltage	Order No.	List Price $ 1 unit	Weight approx. kg	Pack
	**Foot with pipe (100 mm)**					0.1	
	Foot, single	Plastic foot with pipe		**8WD43 08-0DA**①	**49.00**	0.05	
		Plastic for mounting on pipes		**8WD43 08-0DB**②	**12.80**		
		Cast-iron foot for pipe mounting > 400 mm		**8WD43 08-0DC**③	**28.00**		
						0.3	
	**Connecting socket for foot**	Side cable outlet		**8WD43 08-0DD**④	**19.30**	0.2	
		Side cable outlet, with magnetic base[1])		**8WD43 08-0DE**⑤	**126.00**	0.4	
		1/2" NPT Adapter		**8WD43 08-0DF**	**16.00**		
	Pipe, single	100 mm		**8WD42 08-0EF**	**16.70**	0.03	
		150 mm		**8WD43 08-0EE**	**45.00**	0.05	
		250 mm		**8WD43 08-0EA**	**19.30**	0.1	
		400 mm		**8WD43 08-0EB**	**28.00**	0.2	
		1000 mm		**8WD43 08-0ED**	**66.00**	0.4	
8WD43 08-0CA 	**Bracket for wall mounting**						
	• for single-sided mounting			**8WD43 08-0CA**	**20.50**	0.1	
	• for double-sided mounting			**8WD43 08-0CB**	**20.50**		
8WD44 28-0BA 	**AS-Interface adapter element [2])**						
	• without ext. auxiliary voltage	4 signalling elements up to 200 mA max. are possible	24 V	**8WD44 28-0BA**	**225.00**	0.1	
	• with ext. auxiliary voltage	4 signalling elements up to 1,5 A max. are possible	24 V	**8WD44 28-0BB**	**250.00**		
8WD43 58-1XX 	**Lamps**						
	Base BA 15d, 5 W		24 V 115 V 230 V	**8WD43 28-1XX** **8WD43 48-1XX** **8WD43 58-1XX**	**6.40** **6.40** **6.40**	0.01	
	**LEDs**						
	Base BA 15d	red green yellow clear blue	24 V UC	**8WD44 28-6XB** **8WD44 28-6XC** **8WD44 28-6XD** **8WD44 28-6XE** **8WD44 28-6XF**	**90.00** **90.00** **90.00** **90.00** **90.00**		
		red green yellow clear blue	AC 115 V	**8WD44 48-6XB** **8WD44 48-6XC** **8WD44 48-6XD** **8WD44 48-6XE** **8WD44 48-6XF**	**90.00** **90.00** **90.00** **90.00** **90.00**		
		red green yellow clear blue	AC 230 V	**8WD44 58-6XB** **8WD44 58-6XC** **8WD44 58-6XD** **8WD44 58-6XE** **8WD44 58-6XF**	**90.00** **90.00** **90.00** **90.00** **90.00**		
	**Bracket for pipe mounting**			**8WD44 08-0CC**	**21.00**		
	**Bracket for floor mounting**			**8WD44 08-0CD**	**21.00**		

1) For horizontal mounting, only 1 element is recommended.

2) Operation necessitate mounting as the lowest element on signal column.

Downloaded from Arrow.com.