

## Han HPR SP2-CM-SCL-without lanyard



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 021 5412
Specification	Han HPR SP2-CM-SCL-without lanyard
HARTING eCatalogue	<a href="https://harting.com/09400215412">https://harting.com/09400215412</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® HPR
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for panel feed through housing

### Version

Size	SP2
Locking type	Screw locking
Details	Please note that when using the metal protection cover the connectors only can be used without voltage applied or a reduced voltage of max. 2000V. Please note that the use of the protection cover is needed to protect the Han® HC 650 / HC 800 when dropped acc. IEC 61984.

### Technical characteristics

Tightening torque (screw locking)	6 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance  
Since 1945

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	107 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140422513
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467