



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	REVISED PER ECN-22-150900	27APR2022	RK	CSD



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
8 AWG SOLID OR STRANDED	8 AWG STRANDED	8 AWG SOLID OR STRANDED

- 1 STAMP AMP 8* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 0.00254 [.000100] MIN TIN PLATE PER ASTM B-545
- 4 LONGER WIRE BARREL THAN OTHER #8 AWG, PROPER WIRE STRIP LENGTH: 9.12-9.94 [.359-.390]; IGNORE TOOLING INSTRUCTION SHEET STRIP LENGTH
- 5 UL 486 A-B



1000	ON TAPE, REEL	2-31808-2
100	LOOSE PIECE	31808
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-24-93		TE Connectivity		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F] MAX		CHK DA PATTERSON 3-24-93		NAME		
	VOLTAGE RATING: N/A		CIRCULAR MIL AREA: 6.64-10.5mm²[13,100-20,800] SOLID OR STRANDED		APVD JL MECKLEY 3-24-93				
	FOR APPLICATION TOOLING ASSISTANCE CENTER		FOR ORDER ENTRY 1-800-526-5142		PRODUCT SPEC 5		TERMINAL, RING TONGUE, SOLISTRAND 8 AWG		
TOOLING INFORMATION 1-800-722-1111		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C-31808
						WEIGHT -	SCALE 4:1	SHEET 1 OF 1	REV F3
				MATERIAL 2	FINISH 3	CUSTOMER DRAWING			