

Universal Reversible USB 2.0 Cable (Reversible A to Reversible A M/M), 6 ft. (1.83 m)

MODEL NUMBER: **UR020-006**



Reversible USB connector plugs in any direction

Features

- USB 2.0 Male-to-Male, with Universal / Reversible connectors
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold contacts and molded ends provide a lifetime of use

Specifications

OVERVIEW	
UPC Code	037332179395
Technology	USB 2.0 (High Speed)
Cable Type	Passive
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06

Highlights

- 6ft, USB 2.0, Male-to-Male
- Universal, Reversible connector allows plugging in any direction

System Requirements

- Computer with USB A-Female port
- USB device or Patch port with USB A-Female port

Package Includes

- 6-ft. (1.83 m), USB 2.0, Male-to-Male Universal / Reversible Cable

ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	REVERSIBLE USB A (MALE)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty