
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2014
© COPYRIGHT 2001 BY TE CONNECTIVITY ALL RIGHTS RESERVED.

LOC	DIST


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER E.O. P20338	05NOV2009	RM	RDR
	C	REVISED PER E.O. P20483	28MAY2010	RM	RDR
	C1	REVISED PER ECO-14-016535	31OCT2014	JA	DM
	C2	REVISED PER PCN-24-225053	01OCT2024	RK	CB




CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE [mm²] REF. ⚠1 ONLY
16	.053 [1.35]	.120 [3.05]	14-20 AWG [2.5-0.5]

RECOMMENDED MOUNTING DETAIL







3 MATERIAL: SHELL: PA66 GF15 (GRAY)
WELD CAP: PA66 GF15 (BLACK)
GROMMET: VMQ (BURNT RED)
INSERTS: STAINLESS STEEL

2. THIS RECEPTACLE MATES WITH DT06-08SA-XXXX PLUG.
(XXXX = ALL MODIFICATIONS).
CONSULT FACTORY FOR ALL MODIFICATIONS.

1 FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS, SEE ENVELOPE DRAWINGS 0425-015-0000 AND 0425-017-0000.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES[mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 [0.64]
4 PLC ±
ANGLES ±0°30'0"

MATERIAL 3

FINISH

DWN	04JUN2001 TESFU YOHANNES
CHK	31OCT2014 RUSSELL MESSENGER
APVD	31OCT2014 DAVID MEYER
PRODUCT SPEC	108-151009
APPLICATION SPEC	114-151009
WEIGHT	44.95g

TE Connectivity

NAME: RECEPTACLE 8 WAY FLANGED CONNECTOR -CL07 MOD DT SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	4AFU8	C-DT04-08PA-CL07	-

Customer Drawing | SCALE 1:1 | SHEET 1 OF 1 | REV C2

1470-19 (3/11)

printed on 4 Nov 2024 13:50 (Eastern Standard Time) from TE354946

Downloaded from Arrow.com.