









RECOMMENDED P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. RATING: 50mA @ 12VDC
- ▲ 5. OPERATING FORCE: 160± 50gf
6. TRAVEL: 0.25+0.2/-0.1mm
7. CONTACT RESISTANCE: 100mΩ MAX.
8. CONTACT MATERIAL: SILVER
9. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE.
10. INSULATION RESISTANCE: 100MΩ MIN. @100VDC
11. ELECTRICAL LIFE: 100,000 CYCLES
12. ▲ DENOTES CRITICAL PARAMETER
13. OPERATING TEMP: -20°C to +85°C
14. PACKAGING: TRAY, 1,200 PCS / TRAY

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100142	UPDATE DIMENSIONS, NOTES	06/17/21	JM	TITLE RT1105AF160Q				000017676
					SCALE	DATE	DR	DWG	REV
					4:1	9/25/2008	BLR	P010055	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED