

By Burndy  
Catalog # YAV9CT9

Uninsulated Ring Terminal For 10 - 9 AWG



## Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

## Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

## Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes
Buy American Compliant	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

## Conductor

Conductor Size	10 - 9 AWG
Conductor - Copper Str Size	9 AWG

Conductor - Copper Str Size	9 AWG
Range	
Conductor Type	CU C Solid-Size;CU C Str-Size

## Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

## Dimensions

Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.39 in
Dimension - Outside Diameter inch	0.23 in
Dimension - Pad Width inch	0.44 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - Stud Size inch	1/4
Dimension - Length Overall inch	1.15 in
Dimension - D inch	0.57 in
Dimension - N inch	0.25 in

## General

Sub Brand	HYLUG
Physical Attribute - Tongue Type	Ring
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 12 Digit	781810025253
UPC 14 Digit GTIN	00781810025253
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810025253

## Logistics

Carton Quantity	200
Pallet Quantity	99999
Minimum Pack Quantity	200

## Product Assets

[Catalog \[English\]](#)

---



A Hubbell brand

© 2025 Hubbell Incorporated. All rights reserved  
BRDY-YAV9CT9-SPEC-EN | REV 9/2025