

ZBFM 6/WH,LGS:1-100 - Zack marker strip



0800284

<https://www.phoenixcontact.com/us/products/0800284>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Zack marker strip, Sheet, white, labeled, printed horizontally: consecutive numbers from 1 ... 100, mounting type: latching, for terminal block width: 6.2 mm, Number of individual labels: 100, text field height: 5 mm, text field width: 5.5 mm



Commercial data

Item number	0800284
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2123
GTIN	4017918005887
Weight per piece (including packing)	5.57 g
Weight per piece (excluding packing)	5.51 g
Customs tariff number	49119900
Country of origin	PL

ZBFM 6/WH,LGS:1-100 - Zack marker strip



0800284

<https://www.phoenixcontact.com/us/products/0800284>

Technical data

Product properties

Product type	Labeled terminal marker
Pitch	6.2 mm

Marking

Number of individual labels	100
Number of individual labels per row	10
Printing direction	printed horizontally
Printing	consecutive numbers from 1 ... 100

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	5.55 mm
Height	6.5 mm
Depth	1.6 mm
Pitch	6.2 mm

Text field

Text field width	5.5 mm
Text field height	5 mm

Standards and regulations

ZBFM 6/WH,LGS:1-100 - Zack marker strip



0800284

<https://www.phoenixcontact.com/us/products/0800284>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

ZBFM 6/WH,LGS:1-100 - Zack marker strip



0800284

<https://www.phoenixcontact.com/us/products/0800284>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBFM 6/WH,LGS:1-100 - Zack marker strip



0800284
<https://www.phoenixcontact.com/us/products/0800284>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com