



Part Number : [1300990174](#)
Product Description : MAX-LOC/Watertite Cord Grips, 3/4" NPT, Straight Male, Body Size F3, Cable Diameter 12.70-15.88mm (.500-.625"), Non-Metallic
Series Number : 130099
Status : Active
Product Category : Cable Grips
Engineering Number : 5634NM



Documents & Resources

Drawings
[1300990174 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130099
Description	MAX-LOC/Watertite Cord Grips, 3/4" NPT, Straight Male, Body Size F3, Cable Diameter 12.70-15.88mm (.500-.625"), Non-Metallic
NEMA Rating	NEMA 3R
Product Name	MAX-LOC,Watertite
Type	Strain Relief Grip
UPC	78678872220

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	12.70-15.88mm (.500-.625")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Nylon
Mesh Length	N/A
Number of Holes	1
O-Ring	N/A
Thread Size	3/4" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>

MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black	<u>1300990150</u>
MAX-LOC O-Ring, 3/4" NPT	<u>1301800333</u>

This document was generated on Sep 22, 2025