


REV.	DATE	DESCRIPTION
A	03/27/05	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN [] ARE IN INCHES AND FOR STARTER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex SMA FEMALE TO BNC FEMALE ADAPTER 242123
8					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	DRAWN	C.R.S.	03/27/05			
7					0.5 - 8mm ± 0.20mm	CHECKED					
6					B - 30mm ± 0.40mm	DESIGNED					
5					30 - 120mm ± 0.50mm	ISSUED					
4					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:	SHEET		1 OF 1			
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	.020 - .315 ± 0.007"	PART NO.					
2	INSULATOR	TEFLON	NATURAL	1	.315 - 1.180 ± 0.015"	PART NO.					
1	BODY	BRASS	NICKEL	1	1.180 - 4.724 ± 0.020"	PART NO.					
	DESCRIPTION	MATERIAL	FINISH	QTY	DD NOT SCALE DRAWING		CADD FILE		C:/242/242123.DWG		