



## Triple Output High Power RGB LED

COM-15200 ROHS ✓

DESCRIPTION

FEATURES

DOCUMENTS

- Size (approx.): 18mm (D) x 8mm (H)
- Aluminum PCB for thermal dissipation
- Operating Voltage:
  - Red: 2.2-2.6V
  - Green: 3.2-3.8V
  - Blue: 3.2-3.8V
- Wavelength:
  - Red: 620nm
  - Green: 520nm
  - Blue: 460nm
- Viewing Angle: 140°

### Tags

COMPONENT

LED

SMD

© images are CC BY 2.0



Previous Versions ▾

## Triple Output High Power RGB LED Product Help and Resources

TUTORIALS

SKILLS NEEDED



### Touch Potentiometer Hookup Guide

OCTOBER 22, 2015

Learn how to use the SparkFun Touch Potentiometer to control lighting, volume or other inputs in your daily life.



### PicoBuck Hookup Guide V12

FEBRUARY 18, 2016

The PicoBuck board is a high-efficiency three-channel constant-current LED driver.



### FemtoBuck Constant Current LED Driver Hookup Guide V12

DECEMBER 10, 2015

The FemtoBuck board is a high-efficiency, single-channel constant-current LED driver.

COMMENTS

0

REVIEWS

0

## Looking for answers to technical questions?

We welcome your comments and suggestions below. However, if you are looking for solutions to technical questions please see our [Technical Assistance](#) page.

[Log in](#) or [register](#) to post comments.




## STAY IN TOUCH WITH US

Weekly product releases, special offers, and more.



### ABOUT SPARKFUN

[Read Our Story](#)  
[Press & Media](#)  
[SparkFun Education](#)   
[Job Openings](#)

### PARTNER WITH US

[See Our Partners](#)  
[Become a Distributor/Reseller](#)  
[Receive Volume Discounts](#)  
[Build a Custom Kit](#)  
[Apply for a Hardware Donation](#)

### SUPPORT

[Customer Support](#)  
[Purchase Orders & Payment](#)  
[Terms](#)  
[Technical Assistance](#)  
[FAQs](#)  
[Contact Us](#)

### SITE INFORMATION

[Terms of Service](#)  
[Privacy Policy](#)  
[Compliance](#)  
[Site Map](#)

SparkFun Electronics ® / **6333 Dry Creek Parkway, Niwot, Colorado 80503**

Questions? Feedback? powered by [Olark live chat software](#)