





Certifications & Ratings

- RoHS compliant

Features & Benefits

- Compatible with automatic placement equipment
- Packaged in 8 mm tape, 7" reel (4000 pcs/reel) and 20 per strip
- Meets EIA-481-1 pkg. std.

Dimensions




Part Number Guide

Part Number Guide										RoHS Compliant		
5	9	9	-	0	1	X	X	-	0	0	X	F
Color							Packaging Option					
	Red	1	0			2	20 piece tape					
	Red-Orange	2	0			7	7" reel 4000 pcs/reel					
	Orange	3	0									
	Yellow	4	0									
	Yellow-Green	6	0									
	Green	8	1									
	Blue	9	1									


Tape

Tolerance ± 0.1 mm unless otherwise noted




Reel


Tolerance ± 0.1 mm unless otherwise noted



Soldering



Reflow Profile








Electrical/Optical Characteristics

Electrical/Optical Characteristics					Luminous Intensity		Dominant Wavelength		Forward Voltage		Viewing Angle (°deg.)	Thermal Resistance (°C/W)	Reverse Current Intensity (μA)	
Dialight P/N		Emitted Color	Material	Lens Color	If = 20 ma							Rth(j-s) If=20 ma	(Ir) VR=5V	
20-Piece Tape	7" Reel, 4000 pcs				Min	Typ	Min	Typ	Max	Typ				Max
599-0110-002F	599-0110-007F	● Red	AlInGaP	Non Diffused	15	29	625	633	640	2.1	2.5	140	450	10
599-0120-002F	599-0120-007F	● Red-Orange			90	138	620	625	630	2.1	2.5			
599-0130-002F	599-0130-007F	● Orange			53	95	600	605	610	2.1	2.5			
599-0140-002F	599-0140-007F	● Yellow			68	112	585	590	595	2.1	2.5			
599-0160-002F	599-0160-007F	● Yellow-Green			9	43	562	569	575	2.1	2.5			
599-0181-002F	599-0181-007F	● Green	InGaN		195	340	520	525	530	3.2	3.6			
599-0191-002F	599-0191-007F	● Blue			68	105	465	470	475	3.2	3.6			

Absolute Maximum Ratings @ Ts=25 °C

Power Dissipation (mW)	72	105	● G - InGaN
Forward Current (mA)	30	70	● B
Reverse Voltage (V)	5		
Operating Temp (°C)	-40 to +100		
Storage Temp (°C)	-40 to +100		
Peak Pulse Fw Current (mA)	60		
Electrostatic Discharge (HBM) (V)	2000	1000	● G - InGaN ● B
Junction Temp (°C)	105		



Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.