
Downloaded from Arrow.com.



PART NO.	HOLDING DIA. "D"	"E" REF.	"T"	"W"
AL2A	1/8 (3.2)	.46 (11.7)	1/32 (0.8)	3/8 (9.5)
AL3A	3/16 (4.8)	.50 (12.7)		
AL4A	1/4 (6.4)	.53 (13.5)		
AL5A	5/16 (7.9)	.56 (14.2)		
AL6A	3/8 (9.5)	.59 (15.0)		
AL7A	7/16 (11.1)	.62 (15.7)		
AL8A	1/2 (12.7)	.65 (16.5)		
AL9A	9/16 (14.3)	.75 (19.1)		
AL10A	5/8 (15.9)	.78 (19.8)		
AL11	11/16 (17.5)	.81 (20.6)	1/16 (1.6)	1/2 (12.7)
AL12	3/4 (19.1)	.84 (21.3)		
AL14	7/8 (22.2)	.90 (22.9)		
*AL15	15/16 (23.8)	.93 (23.6)		
AL16	1 (25.4)	.96 (24.4)		
AL18	1-1/8 (28.6)	1.05 (26.7)		
AL20	1-1/4 (31.8)	1.11 (28.2)		

*PARTS AVAILABLE BY SPECIAL ORDER ONLY.

NOTES:
1. MAT'L: ALUMINUM ALLOY 5052 H-32 (RMS-199)

REV	DESCRIPTION	ENGR DATE
E	SEE CO 200508 FOR CHANGES	SK 03.11.10
D	SEE CO 200432 FOR CHANGES	SK 09.08.09
C	SEE ECN #927 FOR CHANGES	SK 01.31.05
B	DRAWING UPDATED AND CHANGED FILE NO.	SM 09.26.01
A	CONVERTED TO ACAD	PB 01.18.95

TITLE: CABLE CLAMPS, ALUMINUM

DWG IN IN (MM)

TOLERANCES UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

FILE # AL
MAT'L: SEE NOTES
RE: RICHCO, INC.

DWN: P.B. APP:
DT: 01-18-95 DT:

RICHCO INC.
PO BOX 804238,CHICAGO,60680
(773) 539-4060

FINAL.

PART # AL SERIES

PRINT TYPE CA